NEW! Near Infrared in Real Time

Now includes auto contrast and edge enhancement

IR-1000 Real Time CCD Camera

- High sensitivity
- Near infrared
- New! Automatic contrast
- New! Edge enhancement

The newly designed IR-1000 infrared CCD camera is ideal for applications requiring high sensitivity in the near infrared. The high gain of the camera enables users to detect images in real-time (30 frames/sec.) even when energy levels are very low.

With wide range gain and black level controls, the IR-1000 enables the user to enhance image contrast and offers the ability to apply short-term integration for increased sensitivity. New features such as automatic contrast and edge enhancement offer users greater control and easier use than ever before in this unique one-of-a-kind product from Dage-MTI.



Dage-MTI IR-1000 Infrared CCD Camera and control unit

Ideal for applications such as...

- Electrophysiology
- Fluorescence Microscopy
- Brightfield, Phase Contrast, and Darkfield Microscopy
- Semiconductor Inspection
- Manufacturing Quality Control
- Failure Analysis
- Forensic Analysis



High Sensitivity in Near IR

- Excellent sensitivity in near IR and entire visible spectrum response from 380 nm to 1200 nm
- Provides 5 times more sensitivity at 900 nm

NEW Automatic Contrast

- Electronics instantaneously readjust for optimum contrast
- Useful when changing magnification levels, specimens and/or lighting levels

NEW Edge Enhancement

- Real-time edge enhancement sharpens edges
- Delivers clearer picture by resolving fine details in the image



IR-1000 Real Time CCD Camera

SPECIFICATIONS

Pick-Up Device Signal-to-Noise Ratio Shading Sensitivity Minimum Illumination Gamma Correction Gain/Black Level Electronic Shutter

Active Picture Elements Picture Element Size Horizontal Resolution Pixel Clock Frequency Vertical Rate Horizontal Rate

Lens Mount

Options

Operating temperature Input voltage

1/2" interline CCD with microlens >56dB <5% overall .00035 fc (.0035 lux) Gamma set to 1.0 at factory Switchable fixed or automatic (100:1)


RS-170 768 (H) x 494 (V) 8.5um (H) x 9.8um (V) 570 TVL 14.318 mHz 59.94 Hz 15,734 Hz

"C" mount Computer interface Investigater 1/2" optical coupler


0°C to +40°C 95 VAC to 250 VAC

.05fc (0.5 lux) on sensing area @ 3200K Nine-step manual to 1/10,000 IR-1000 IR-1000 E

CCIR 752 (H) x 582 (V) 8.6um (H) x 8.3um (V) 560 TVL 14.1875 mHz 50 Hz 15,625 Hz



- Real-time edge enhancement greatly increases fine detail
- Automatic contrast When a scene changes, the electronics automatically and instantaneously readjust to achieve optimum contrast



Auto contrast with dark object in field of view

Auto contrast without dark object in field of view

- High sensitivity
- Near infrared
- New! Automatic contrast
- New! Edge enhancement



Dage-MTI IR-1000 Infrared CCD Camera and control unit

Features:

- NIR Spectral Response
- High Sensitivity
- Two-Piece Design
- Wide Range Automatic Gain
- Wide Range Black Level
- Ten-Step Grey Scale Test Signal
- On-Chip Integration

DAGE-MTI

For more information, call (219) 872-5514 or visit www.dagemti.com.

Call today for product specs, demo, or to place an order.

®2012 Dage-MTI, All Rights Reserved